


Left Side

Connector(s): MT-RJ SECURE (No Pins)
Mode: MM
Housing Color: Red
Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A - ——— - B
Fiber B - ——— - A

Notes:

- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).
- 4 OM3 assemblies tested at 850nm, all other multimode tested at 1300nm

Right Side

Connector(s): SC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

LOC
CE
DIST
16

P	LTR	REVISION RECORD	DATE	DWN	APVD
B2		REVISED PER ECO-11-005139	14APR11	RK	HMR

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± . 4 PLC ± .

DWN Cable Assy Configurator		MATERIAL -	HEAT TREAT -
b:	CHK Doug Kirsch	 TE Connectivity	
	APVD Doug Kirsch		
	NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex		
SCALE NTS	SIZE A2	DRAWING NO C- 6278894	SHEET 1 of 3
			REV B2

8

7

6

5

4

3

2

1

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Red		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6278894-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-6278894-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-6278894-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-6278894-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-6278894-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-6278894-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	-
0-6278894-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	-
0-6278894-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	-
0-6278894-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-6278894-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-6278894-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	-
1-6278894-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-6278894-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	-
1-6278894-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	-
1-6278894-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	-
1-6278894-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	-
1-6278894-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-6278894-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	-
1-6278894-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	-
2-6278894-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-6278894-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	-
2-6278894-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	-
2-6278894-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	-
2-6278894-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	-
2-6278894-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	-
2-6278894-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	-
2-6278894-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	-
2-6278894-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	-
2-6278894-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	-
3-6278894-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	-
3-6278894-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	-
3-6278894-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	-
3-6278894-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	-
3-6278894-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	-
3-6278894-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	-
3-6278894-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	-
3-6278894-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	-
3-6278894-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	-
3-6278894-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	-
4-6278894-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	-
5-6278894-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-

Qty	U of M	Description	Item No
2	piece	Trace Label	16
2	piece	CONN SUBASSY, MM, SC 1.6MM	15
2	piece	Eyelet/Shrink tube assembly - White	14
2	piece	SC Duplex Clip	13
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
AR	meter	2 fiber, 62.5/125, 1.8 mm, Twinzip, Orange, OFNR (Riser)	11
2	piece	2.5mm ferrule cover	10
2	piece	SC Simplex Housing, Beige	9
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	8
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	MT-RJ Keyed Connector Housing - Red	6
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	PIN KEEPER, 3.8MM	3
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	DUST COVER, MT-RJ	1

LOC
CE
DIST
16

P	LTR	SEE SHEET 1				-	
		REVISION RECORD			DATE	DIN	A

DIMENSIONS:
meters



TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-

Part: Cable Assy Configurator		MATERIAL: -		HEAT TREAT: -	
OK: Doug Kirsch					
APPROVED: Doug Kirsch					
NAME: FO C/A - 2 fiber, 62.5/125, OM3R (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex					
SCALE: NTS	SIZE: A2	DRAWING NO: C- 6278894	SHEET: 2 of 3		REV:

Per specification 107-1645-1

[illegible]

Made in XXX

X-XXXXXXXX-X

—Trace # - Bar Code

—Trace # - Human Readable

—Part Number

—Country of Origin

This label is used on all lengths on this drawing.

Per specification 107-1645-1



XXXXXXXXXXXXXXXXXXXX

Made in XX

X-XXXXXXXX-X

Trace # - Bar Code

Trace # - Human Readable

Part Number

—Country of Origin

This label is used on all lengths on this drawing.

LOC
CE
DIST
16

		SEE SHEET 1			
P	LTR	REVISION RECORD	DATE	DIN	A

DIMENSIONS:
meters



TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-

Part Cable Assy Configurator		MATERIAL -	HEAT TREAT -
OK Doug Kirsch	 TE Connectivity		
AP'D Doug Kirsch			
NAME FO C/A - 2 fiber, 62.5/125, OM3R (Riser) jacket, MT-RJ SECURE (No Pins) to SD-Duplex			
SCALE NTS	SIZE A2	DRAWING NO C- 6278894	SHEET 3 of 3
			REV 1