

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		AA	REV PER ECO-12-012918	09JUL2012	JM	JG

- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: HOUSING—POLYCARBONATE,CLEAR.
TERMINAL—0.36[.014] THICK PHOSPHOR BRONZE PLATED WITH 1.27μm[.000050] THICK GOLD IN LOCALIZED GOLD PLATE AREA, OVER 2.54μm[.000100] THICK NICKEL UNDERPLATE.
- 3

PLUG WILL ACCEPT 26 OR 28 AWG STRANDED OR TINSEL WIRE HAVING AN INSULATION DIAMETER OF 0.89 – 0.99[.035 – .039] AND A MAXIMUM OVAL CABLE JACKET OF 2.29 × 6.61[.090 × .260].
- 4


TERMINATED DIMENSION 6.15[.242] MAXIMUM.
- 5

10 ASSEMBLIES PER PACKAGE.
- 6


10,000 ASSEMBLIES PER PACKAGE.
- 7

1000 ASSEMBLIES PER PACKAGE.
- 8

100 ASSEMBLIES PER PACKAGE.



SUPERSEDED BY 5-641337-4	5	6-641337-3
	8	5-641337-3
	7	5-641337-2
	6	5-641337-1
SUPERSEDED BY 5-641337-2	REELED 10	641337-1
	PACKAGED	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YTP/UTA 9-3-93		 TE Connectivity		
		CHK C.WHITT 9-15-93				
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME MODULAR PLUG ASSEMBLY, 6 POSITION, LINE -		
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - 				
MATERIAL - 		FINISH - 		PRODUCT SPEC 108-1163		SIZE A2
				APPLICATION SPEC 114-6016		
				WEIGHT -		DRAWING NO C-641337
				CUSTOMER DRAWING		
						SCALE 4:1
						REV AA