

Amphenol® RF
Global RF Solutions

☐ Part Number
 ☒ Text
 ☐ RoHS Compliant

[products](#)
[site tools](#)
[rf made simple](#)
[distributors](#)
[about us](#)
[newsletter](#)
[contact us](#)
[login](#)

Toll Free: (800) 627-7100
 Inside CT: (203) 743-9272

[Locate A Distributor](#) [Check Distributor Inventory](#)

[Customer Drawings](#) [Assembly Instructions](#) [Catalog](#)

[Product Overview](#) [Product Search](#) [Cross Reference](#) [QPL Products](#) [Markets Served](#) [Product Literature](#)

[Customer Extranet](#) [Salesperson Extranet](#) [Vendor Extranet](#) [Employee Extranet](#) [Internal Employee Extranet](#)

product details

Product Search

[1.0/2.3](#)
[1.6/5.6](#)
[AFI](#)
[AMC](#)
[BNC / RP-BNC](#)
[C](#)
[FAKRA SMB](#)
[FME](#)
[HD BNC](#)
[HN](#)
[MCX](#)
[Mini BNC](#)
[Mini UHF](#)
[Mini 75 \$\Omega\$ SMB](#)
[MMCX](#)
[Precision \(APC\)](#)
[QMA](#)
[SC](#)
[SMA / RP-SMA](#)
[SMB](#)
[SMC](#)
[SMP](#)
[SSMB](#)
[TNC / RP-TNC](#)
[Triax](#)
[True 75 \$\Omega\$ BNC](#)
[Twin BNC](#)
[Twinax](#)
[Type F](#)
[Type G](#)
[Type N](#)
[UHF](#)
[Reverse Polarity](#)

[Adapters](#)
[Tools](#)
[Accessories](#)

[Product Search](#)

src="/images/dottedline.gif"

[Inventory Search](#)

image
not yet
available

Please note: Images are for reference only

Amphenol Part Number: 082-61
Product Series: [Type N](#)
Product Type: [Connectors](#) » [Cable](#)
Body Plating: [Nickel](#)
Cable Group: [G4](#)
Cable Type: [213.9](#)
Connector Body Style: [Straight](#)
Contact Plating: [Nickel](#)
Gender: [Plug](#)
Impedance: [50 Ohm](#)
RoHS Certificate: [Yes](#)
IGS File Download: [IGS File](#)
More Information: [Distributor Inventory](#)

