

The CADDY® CAT-CM Cable Support System provides a convenient pathway for wires and cables. Specially designed U-Hooks and Double J-Hooks have large-diameter, rounded support surfaces/edges to avoid over-bending and kinking of cables. The U-Hooks are available in a range of sizes for different cable capacity needs.

CADDY CAT-CM is UL® listed and complies with the provisions of ISOSM/IECSM 18010 "Pathways and spaces for customer premises cabling" and with the provisions of TIASM-569-A "Commercial Building Standard For Telecommunications Pathways and Spaces."



Two Major Installation Options:



The **Rod-Mounted Option** allows for field assembly of the hooks onto All-Thread Rod (ATR). Other benefits include:

- Customized intervals between hooks
- Easy level changes – under or over ductwork, piping, etc. – no fittings necessary
- Direct attachment to the ceiling or building structure with threaded rod and CADDY® Fasteners
- U-Hooks to be mounted on a base (e.g., Pipe Pier™) in raised floor applications, allowing for a large amount of cables to be organized and neatly routed

The **Cantilever-Mounted Option** consists of U-Hooks being mounted with brackets to walls and columns. This option allows for:

- Cable runs along walls
- Specification of individual hook spacing as needed
- Mounting of cabling within existing column grid

| UPC Code 782856- | Part Number | CSC Part Number | Description | Rod | Cantilever | Qty per Box / Case | Weight per Box (Lbs) |
|---------------------|-------------|-----------------|--------------------------------|-----|------------|--------------------|----------------------|
| 46614 | CAT100CM | 590969 | Double J-Hook 2x50 mm = 100 mm | ✓ | | 25/150 | 7.5 |
| 46486 | CAT200CM | 590970 | U-Hook 200 mm with T-nut | | ✓ | 10/50 | 6.0 |
| 46489 | CAT200CMLN | 591523 | U-Hook 200 mm less nut | ✓ | | 10/50 | 5.0 |
| 46485 | CAT300CM | 590977 | U-Hook 300 mm with T-nut | | ✓ | 10/50 | 7.0 |
| 46490 | CAT300CMLN | 736871 | U-Hook 300 mm less nut | ✓ | | 10/50 | 6.0 |
| 46497 | CATTBCM | 590987 | Protection tube | ✓ | | 30/300 | 3.5 |
| 47336 | CATWMCM | 754289 | Wall Bracket | | ✓ | 10/NA | 8.5 |
| 46496 | CATRT200CM | 590992 | Wire Retainer 200mm/8" | ✓ | ✓ | 60/NA | 7.5 |
| 46495 | CATRT300CM | 590993 | Wire Retainer 300mm/12" | ✓ | ✓ | 50/NA | 10.0 |

CABLE CAPACITY CHART

| Cable | CAT100CM on ATR | CAT200CM on ATR or Cantilever | CAT300CM on ATR or Cantilever |
|----------------------|-----------------|-------------------------------|-------------------------------|
| 4-pair UTP, Cat 5/5e | 80 | 500 | 750 |
| 4-pair UTP, Cat 6 | 50 | 315 | 470 |
| 4-pair ScTP/FTP | 40 | 250 | 375 |
| 4-pair STP | 26 | 170 | 250 |

Distributed by:



www.gocsc.com
1.877.462.7279

IEC is a service mark of Independent Electrical Contractors, Inc. ISO is a service mark of International Organization for Standardization. Pipe Pier is a trademark of Pipe Pier Inc. TIA is a service mark of Telecommunications Industry Association. UL is a registered trademark of Underwriters Laboratories, Inc.

WARNING – ERICO products shall be used only as illustrated and recommended in the product instruction sheets (additional instruction sheets are available at www.erico.com). Misuse or misapplication may cause failure resulting in possible property damage or bodily injury.

Copyright ©2005 ERICO International Corporation. All rights reserved.
CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

