

MC08110 - ANALOG STATION SET & CENTRAL OFFICE LINE PROTECTOR

ORDERING INFORMATION

ITW Linx Part Number	Description
MC08110	Protects up to 16-wires (8-pairs) using 110 punchdown block on the Input and 110 punchdown block on the Output.

* Questions about ordering? Please contact us at **1-800-336-LINX** / Contact an authorized distributor for pricing * (MOQ: 6)

TECHNICAL SPECIFICATIONS

PRODUCT SPECIFICATIONS:

Agency Approval	UL 497A (Secondary)
Grounding Requirements	Uses Electrical AC Ground
.....	for use with SurgeGate Series AC Base Units.
.....	See Technical Reference page 83-84 for additional grounding tips.
Recommended Grounding Impedance	<0.5 Ohm
Width	5.87"
Height	4.25"
Depth	1.5"
Weight	0.45 lbs
Product Warranty	Lifetime
Connected Equipment Warranty	Up to \$50,000

SIGNAL LINE SURGE PROTECTION: (TELCO)

Signal Perfect Circuitry	Yes
Auto-Resetting PTCs	160 mA (8-10 Ohms)
Clamping Level	260V (T-R, T-G, R-G)
Response Time	1-5 Nanoseconds
Capacitance	<50pF
Suppression Modes	Metallic & Longitudinal
Wires Protected	16-wires (8-pairs)
Termination Type	110 punchdown



MODULAR PROTECTOR

SURREGATE SERIES

Features:

- **Auto-Resetting Technology** - PTC resistors open when a surge occurs, protecting your equipment, but unlike other fuses, the PTCs close again once the surge passes. Less downtime, and less service calls
- **Expandable System Protection** - SurgeGate Series Base Units and Modules can be attached to expand system protection as your system grows
- **Lifetime Product Warranty** - This surge protector shall be free of any defects in design, materials, or workmanship, or ITW Linx will repair or replace the defective product
- **\$50,000 Connected Equipment**
- **AVAYA approved products:**
146K, 700209810

AVAYA
Approved Product

For up-to-date warranty information, please visit our web site at www.itwlinx.com.



Signal Perfect™

