



UP3P - 66 BLOCK, UL SECONDARY SURGE PROTECTORS

ORDERING INFORMATION

ITW Linx Part Number	Description
UP3P-27	UL Secondary listed with 160mA PTC for voice / fax / modem lines (27V).
UP3P-39	UL Secondary listed with 160mA PTC for voice / fax / modem lines (39V).
UP3P-75	UL Secondary listed with 160mA PTC for voice / fax / modem lines (75V).
UP3P-235	UL Secondary listed with 160mA PTC for voice / fax / modem lines (235V).

* Questions about ordering? Please contact us at **1-800-336-LINX** / Contact an authorized distributor for pricing * (Above products have to be purchased of minimum 25, multiple 5 after)

Features:

- **Dual Indicator Lights** - Protection OK and Ground Connection OK
- **Solid-state Protection** - Provides the fastest response
- **Single Pair Protection** - Scale the protection to the system size. Protect only the lines requiring protection
- **Streamlined Installation**- Eliminate redundant cross-connects by adding protection directly at the 66 Block. Press fit protectors to the block and attach the ground bar to the protectors. A Screw Ground Lug also is required. (MGBSGL-1)
- **Sneak Current Protection** - Protects against fires caused by overloads and power crosses
- **Cost Savings** - Eliminate expensive five-pin blocks and use economical 66 Blocks
- **Optimum Protection** - Available in a number of voltage ratings to match system operating voltages
- **Ideal for Retrofit Applications** - Just remove the bridging clips from the block & replace them with the UltraLinX Protector, add the ground connection and the pair is protected
- **Lifetime Product Warranty** - This surge protector shall be free of any defects in design, materials, or workmanship, or ITW Linx will repair or replace the defective product

For up-to-date warranty information, please visit our web site at www.itwlinx.com.



Signal Perfect™



TECHNICAL SPECIFICATIONS

PRODUCT SPECIFICATIONS:

Agency Approval	UL 497A (Secondary)
LED Indicators	Yes
Sneak Current Protection	Yes
Grounding Requirements	Field installed solid copper wire
.....	for Secondary 1-6 pairs 14 AWG
.....	for Secondary 7-25 pairs 6 AWG
Recommended Grounding Impedance.....	<0.5 Ohm
PTC Rating.....	160mA (8-10 Ohms)
Applications.....	Data / Voice / Fax / Modem lines
Width.....	1.88"
Height.....	2.62"
Depth	0.38"
Weight.....	0.04 lbs
Product Warranty	Lifetime

TELCO CIRCUIT PROTECTION

Signal Perfect Circuitry	Yes
Auto-Resettable	Yes
Clamping Level	27V, 39V, 75V, 235V
Response Time	1-5 Nanoseconds
Capacitance.....	<50pF
Suppression Modes	Metallic & Longitudinal
Wires Protected	2-wires, 1-pair
Termination Type	66 type M Blocks



ULTRALINX
 SERIES
 66 BLOCK SURGE
 PROTECTOR

