

M2C - ADVANCED SERIES 2-OUTLET DIRECT PLUG-IN SURGE PROTECTOR

ORDERING INFORMATION

ITW Linx Part Number	Description
M2C	2-outlet AC surge protector, with Protect or Disconnect circuitry and integrated cable management. Plus protection for one cable TV, modem or HDTV line.

* Questions about ordering? Please contact us at **1-800-336-LINX** / Contact an authorized distributor for pricing * (MOQ: 24)

TECHNICAL SPECIFICATIONS

PRODUCT SPECIFICATIONS:

Agency Approval	UL 1363, 1449
LED Indicators	2
Grounding Requirements	Uses Electrical AC ground,
Width / Height / Depth / Weight	3.5" / 5.5" / 2" / 0.74 lbs
Product Warranty	Lifetime

COAX CIRCUIT PROTECTION

Signal Perfect Circuitry / Fuseless	yes
Response Time	1-5 Nanoseconds
Termination	Female "F" Type
Antenna/Cable Lines Protected	1-line
Antenna/Cable Clamping Level.....	0.7V
Antenna/Cable Insertion Loss.....	< 1db

AC SURGE PROTECTION

Thermal Fusing / Catastrophic Surge Circuit	Yes
Single Pulse Energy Dissipation	1350 Joules
Peak Impulse Current.....	52,000 A
EMI/RFI Noise Filtration.....	50db (99.7%)
Line Voltage	120V (50/60Hz)
Initial Clamping Level.....	200V Peak, 141 Rms
UL 1449 Rating.....	400V
Protection Modes.....	L-N, L-G, N-G
Maximum Current Rating	15A (1800W)
Response Time	1-5 Nanoseconds
Plug Configuration	Direct Plug-in
Number of Outlets.....	2



2 OUTLET DIRECT PLUG-IN SURGE PROTECTOR WITH COAX PROTECTION

M2 SERIES



Features:

- 2-outlet AC protection
- Direct Plug-in
- Coax protection for cable modem, cable TV or HDTV line
- Diagnostic indicator lights (2)
- EMI/RFI noise filtration
- Integrated cable management
- Enhanced backlight
- **Lifetime Product Warranty** - This surge protector shall be free of any defects in design, materials, or workmanship, or ITW Linx will repair or replace the defective product

For up-to-date warranty information, please visit our web site at www.itwlinx.com.



Signal Perfect™

