



6			5			4			3			2			1		
ITEM NO.	DESCRIPTION	QTY.				CATALOG NO.	DESCRIPTION	LENGTH	BUFFER COLOR	HOUSING COLOR	BOOT COLOR						
1	LC CONNECTOR DUST CAP	1				FPLCC3MM	LC 62.5/125um MULTIMODE PIGTAIL	3 METER	ORANGE	BEIGE	BLACK						
2	LC CONNECTOR BODY	1				FPLCD3MM	LC 50/125um MULTIMODE PIGTAIL	3 METER	WHITE	BEIGE	BLACK						
3	LC CONNECTOR BOOT	1				FPLCS3SM	LC 9/125um SINGLEMODE PIGTAIL	3 METER	YELLOW	BLUE	BLUE						
4	900um BUFFERED CABLE	A/R				FPLCE3MM	LC 50/125um ENHANCED MULTIMODE PIGTAIL	3 METER	AQUA	BEIGE	BLACK						



NOTES:

- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-B.3 SPECIFICATIONS.
- CONNECTOR USES A PC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
- CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN.
- OPTICAL INSERTION LOSS TEST DATA INCLUDED IN EACH BAGGED PIGTAIL.
- 50/125um ENHANCED MULTIMODE FIBER IS RATED FOR 10Gb/s TRANSMISSION FOR UP TO 300 METERS AT 850nm.
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

C	6159	9/28/07	CHANGD BOOT COLORS	CD	
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE:		 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378	
			MATERIAL:		TITLE: FIBER PIGTAIL ASSY, LC SM/MM	
			DRAWN BY: PAUL S. MAGUIRE 01/27/03		SIZE C	DRAWING NO. C11915
			CHECKED BY: JON LUTZEN 01/29/03		REV. C	
		APPROVED BY: JON LUTZEN 01/29/03		SCALE: 1/1		SHEET 1 OF 1