










ITEM NO.	DESCRIPTION	QTY.
1	XCELERATOR HXJU SERIES JACKS	1
2	STUFFER CAP	1

CATALOG NUMBER 25PK	CATALOG NUMBER	COLOR	LASER MARKING
N/A	HXJUB	BLUE	XUB
N/A	HXJUBK	BLACK	XUBK
N/A	HXJUEI	ELECTRIC IVORY	XUEI
N/A	HXJUGN	GREEN	XUGN
N/A	HXJUGY	GRAY	XUGY
HXJUOW25	HXJUOW	OFFICE WHITE	XUOW
N/A	HXJUR	RED	XUR
N/A	HXJUOR	ORANGE	XUOR
N/A	HXJUTI	TELCO IVORY	XUTI
N/A	HXJUW	WHITE	XUW
N/A	HXJUY	YELLOW	XUY
N/A	HXJUAL	ALMOND	XUAL



- NOTES
UNLESS OTHERWISE SPECIFIED:
1. UL LISTED: E129878
 2. CSA CERTIFIED: LR 80837
 3. NOSE CONTACTS ARE BERYLLIUM COPPER WITH 50 MICRO INCH GOLD PLATING IN MATING AREA
 4. IDC CONTACTS ARE TIN LEAD PLATED
 5. ALL CONTACTS ARE UNDERPLATED IN NICKEL
 6. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

D	5682	08/31/05	ADDED ALMOND CATALOG NUMBER	CD	
C	4436	08/31/01	CHANGED GRAPHICS, TOWER AND STUFFER CAP	PSM	
B	4166	03/07/01	REDRAWN	PSM	HKM
A	4160	03/01/01	INITIAL RELEASE	PSM	HKM
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°	PROJECT REFERENCE:	 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378			
		MATERIAL:				
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION	DRAWN BY: P.S.MAGUIRE 03/01/2001	TITLE: XCELERATOR HXJU SERIES JACKS (6 POSITION)			
		CHECKED BY: H. McGREGOR 03/07/2001	SIZE C	DRAWING NO. C11297		REV. D
		APPROVED BY: H. McGREGOR 03/07/2001	SCALE: 2/1		SHEET 1 OF 1	