





ITEM NO.	DESCRIPTION	QTY.
1	PLATE,FLUSH,4P,W/LABELS	1
2	SCREW,6-32 PAN HD-SPECIAL	2
3	CARD,PAPER,.40X1.92,BLANK	2
4	COVER LABEL,CLEAR	2
5	COVER LABEL,MATCHING COLOR	2

CATALOG NUMBER	COLOR	DESCRIPTION
IFP14OW	OFFICE WHITE	PLATE, FLUSH 4 PORT
IFP14EI	ELECTRIC IVORY	PLATE, FLUSH 4 PORT
IFP14W	WHITE	PLATE, FLUSH 4 PORT
IFP14GY	GRAY	PLATE, FLUSH 4 PORT
IFP14TI	TELCO IVORY	PLATE, FLUSH 4 PORT
IFP14BK	BLACK	PLATE, FLUSH 4 PORT
IFP14AL	ALMOND	PLATE, FLUSH 4 PORT
IFP14LA	LIGHT ALMOND	PLATE, FLUSH 4 PORT



KEYSTONE OPENING



- NOTES
UNLESS OTHERWISE SPECIFIED:
1. UL LISTED: E129878
 2. CSA CERTIFIED: LR 80837
 3. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

C	5870	6/8/06	ADDED -LA CATALOG NUMBER	CD	
B	5680	8/22/05	ADDED -AL CATALOG NUMBER	CD	
A	4148	02/22/01	INITIAL RELEASE	PSM	HKM
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER
ANSI Y14.5M-1982
UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES (MM).
TOLERANCES
.XX = ±.01 (.25)
.XXX = ±.005 (.127)
.XXXX = ±.0025 (.0635)
ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS,
BLUEPRINTS, OR SUPPORTING
DOCUMENTATION FOR QUOTATION
OR OTHER PURPOSES, YOU AGREE
NOT TO DISCLOSE TO OTHERS
THE IDEAS, INFORMATION, OR
DESIGNS SHOWN HEREIN, AND
THAT YOU WILL MAKE NO USE
OF SAME WITHOUT PERMISSION


PROJECT REFERENCE:

MATERIAL:

DRAWN BY:
P.S.MAGUIRE 02/22/2001

CHECKED BY:
H. McGREGOR 02/28/2001

APPROVED BY:
H. McGREGOR 02/28/2001



Hubbell Premise Wiring

HUBBELL INCORPORATED (Delaware)

14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE:

INFINE STATION FACE PLATE
FLUSH 4-PORT
WITH LABEL HOLDERS

SIZE

DRAWING NO.

REV.

SCALE:

SHEET

1 OF 1

C

C773066

C