

# SPECIFICATIONS

POH1000/1000HB	
Dimensions	4.375"(H) x 5.625"(W) x 11.00"(L)
Weight	2.8 lbs. (POH1000); 3.35 lbs. (POH1000HB)
Power Source	24VAC, 60Hz
Accessories (supplied)	Camera mounting bolt/plain washer (2pcs.); Housing mounting bolt/plain washer and spring washer for WV-7260D (2pcs.); Housing mount bolt/plain washer and spring washer for P9000H series (2pcs.); Cable strain relief with locknuts (2pcs.)
POH1500/1500HB	
Dimensions	4.375"(H) x 5.625"(W) x 16.00"(D)
Weight	3.3 lbs. (POH1500); 3.85 lbs. (POH1500HB)
Power Source	24VAC, 60Hz
Accessories (supplied):	Camera mounting bolt/plain washer (2pcs.); Housing mounting long bolt/plain washer and spring washer for WV-7260D pan/tilt (2pcs.); Housing mount short bolt/plain washer, spring washer for P9000H series (2pcs.); Cable strain relief with locknuts (2pcs.)
PBK10	
Dimensions	3.00"(H) x 3.00"(W) x 1.50"(D)
Weight	.45 lbs.
Power Source	24VAC, 1.4W

Accessories (supplied)	PCB power board with blower housing and PCB bracket (1pc.); Mounting screws/plain and washers (4pcs.); PCB standoffs (4pcs.); Wire Management Clips (2pcs.)
PBK12	
Dimensions	3.81"(H) x 4.6"(W) x 2.8"(D)
Weight	7.4 oz.
Power Source	24VAC, 50/60Hz
Accessories (supplied)	Powerboard, 1 pc.; Connector, 1 pc.; Pin, 6 pcs.; Mounting screws, 3 pcs.
PHK10	
Dimensions	2.00"(W) x 2.25"(L)
Weight	1 lbs.
Power Source	24VAC, 25 Watts
Accessories (supplied)	PCB power board with mounting bracket (1pc.); Mounting screws/plain and washers (4ea.); PCB stand-offs (4ea.); Wire management clips (2ea.); 1/4" Screw for heater bracket mount (1ea.)
PSS10	
Dimensions	2.15"(H) x 5.80"(W) x 13.25"(L)
Weight	1.1 lbs.
PSS15	
Dimensions	2.15"(H) x 5.80"(W) x 18.25"(L)
Weight	1.5 lbs.

## OPTIONAL ACCESSORIES

POH1000/1000HB
• PSS10
Sun Shield for POH1000
• PHK10
24VAC, 25W heater kit for POH1000
• PBK10
24VAC, 1.4W blower kit for POH1000

POH1500/1500HB
• PSS15
Sun Shield for POH1500
• PHK10
24VAC, 25W heater kit for POH1500
• PBK10
24VAC, 1.4W blower kit for POH1500

## RECOMMENDED MOUNTS

WV-831P	Light duty wall mount with manual adjustable swivel head. Supports up to 20 lbs.	P9000HP	Medium duty pole mount with manual adjustable swivel head. Supports up to 85 lbs.
P9000HW	Medium duty wall mount with manual adjustable swivel head. Supports up to 85 lbs.	P9000HC	Medium duty corner mount with manual adjustable swivel head. Supports up to 85 lbs.

## POH1000/1000HB/1500/1500HB Mounting Variations

