



# SENTROL

## 1285T Series

Designer-Styled Surface Mount with  
Screw Terminals Magnetic Contacts

Gap distance	Closed loop	Open loop	SPDT
Up to 3/4"	1285T		
Up to 1"		1283T	1284T
Up to 1 1/2"	1285TW	1286TW	
Up to 2"		1283TW	1284TW

Color	Natural (off-white)	Mahogany brown	Grey
Quantity	10		



1285T-N



0 46188 02080 5

100% TESTED



## 1285T Series Magnetic Contacts

### Designer-Styled Surface Mount with Screw Terminals

#### Installation Instructions

**1283T, 1284T, 1285T, 1283TW, 1284TW, 1285TW, 1286TW**

Select desired mounting positions for contact and magnet. Important: Align contact and magnet as directed on magnet base (switches are polarity sensitive). Attach contact and magnet to surface. Wire leads to terminals. Snap on cover.

#### UL Specifications

\*\*European Union Specifications: 48 VAC/DC Max., 0.5 Amp

Part Number	Loop Type	Electrical Configuration	Gap Distance*
1283T	Open	N/C	Up to 1"
1283TW	Open	N/C	Up to 2"
1284T	Open or Closed	SPDT	Up to 1"
1284TW	Open or Closed	SPDT	Up to 2"
1285T	Closed	N/O	Up to 3/4"
1285TW	Closed	N/O	Up to 1 1/2"
1286TW	Open	N/C	Up to 1 1/2"

**\*\*FORM A (1285T, 1285TW)**  
Voltage: 100 VAC/DC Max  
Current: 0.5 A Max  
Power: 7.5 W Max

**FORM B (1283T, 1283TW, 1286TW)**  
Voltage: 30 V Max  
Current: 0.25 A Max  
Power: 3.0 W Max

**FORM C (1284T, 1284T)**  
Voltage: 30 V Max  
Current: 0.25 A Max  
Power: 3.0 W Max

\* Gap Specifications are nominal and may vary  $\pm 20\%$ . Gap Specifications are for switch to make. Break distance is approximately 1.1 to 1.5 times make.

#### ULC Specifications

All Contacts: 30 VDC, 50 ma max.

Gap Specifications:\*  
See UL Gap Specifications



PH 503.692.4052

USA & Canada: 800.547.2556

Technical Service: 800.648.7424 FaxBack: 800.483.2495

www.sentrol.com www.interlogixsecurity.com

©2001 Interlogix, Inc.

Interlogix, Caddx, ESL, ITI and Sentrol are trademarks of Interlogix, Inc.