

## New features

- Flash memory microprocessor
- Expanded event log
- Early open/late close reporting
- Programmable loop response

## Standard features

- Expandable to 12 hardwire/16 wireless zones
- Maximum of 8 keypads with up to 8 per partition
- 2 true partitions with separate account codes, entry/exit delays, and feature selections for each partition
- 40 user codes
- 512-event history log that provides date, time, event and user number
- Wireless technology with up to 12 supervised zones
- Hardwire expansion up to 16 zones
- Supports SIA and contact ID communication formats
- CP-01 Compliant

## Overview

The NetworX NX-6 is a full-featured, mid-sized security system that uses advanced technology for burglary, fire and environmental detection. The NX-6 is a flexible security system that is easy to install and simple to use. With two partitions and up to 16 zones, the NX-6 can handle most medium residential and commercial security needs.

## Outstanding features

The NX-6 panel comes standard with six hardwire zone inputs. Four programmable outputs can be set up to activate external devices during an alarm or other system event. The modular design allows for complete integration of multiple systems within one enclosure. Adding more zones or expanding capability is fast and easy.

## Convenient and flexible

Conduct quick and easy on-site programming with alphanumeric keypads and a menu driven text interface. Off-site programming is also available with the DL-900 software for Windows.

# NetworX Control Panel NX-6



## NetworX Control Panel NX-6

### Specifications

- Operating Power – 16.5V AC 40VA
- Auxiliary w/40VA or 50VA transformer – 1 Amp
- Auxiliary w/NX-320E power supply – 3 Amps\*

### Loop resistance

- For standard loop – 300 $\Omega$  Maximum
- For 2-wire smokes – 30 $\Omega$  Maximum

### Operating temperature

- 32 to 120°F

### Dimensions

- 6.40 inches wide
- 4.0 inches high
- 1.10 inches deep

### Shipping weight

- 9 pounds

\* When using the NX-320E (w/50VA transformer) rated at 2 Amps and NX-6 (w/40VA or 50VA transformer) rated at 1 Amp, the combined available power is 3 Amps.

## Available Keypad Styles



LED



LCD with  
Removable Door



Fixed Display with  
Removable Door



LED with  
Removable Door

NetworX Technical Support: 800-727-2339

12345 SW Leveton Drive  
Tualatin, OR 97062  
Phone: 503-692-4052  
USA & Canada: 800-547-2556  
Technical Service: 800-727-2339  
Faxback: 800-483-2495

1275 Red Fox Road  
Arden Hills, MN 55112  
Phone: 651-777-2690  
USA & Canada: 800-777-5484  
Technical Service: 800-777-2624

[www.gesecurity.com](http://www.gesecurity.com)



imagination at work