# **TF Series Power Supply**

## **SINGLE 24 VAC CAMERA POWER SUPPLY, INDOOR**

### **Product Features**

- Cost Effective
- 20 or 50 VA Output
- Fuse Protection
- Class 2 Power Supply

The **TF Series Power Supply** is a 24 VAC, Class 2 power supply that is ideal for use in fixed camera applications.

To meet different installation requirements, two models are available. The **TF2000** provides 20 VA output and the **TF9000** provides 50 VA output.


These economical power supplies, which are for indoor use only, plug into any 120 VAC duplex wall receptacle having a center screw. A mounting screw in the top of the power supply replaces the screw in the center of the receptacle cover to fasten the power supply securely to the receptacle.

Two screw terminals on the power supply provide easy connection of the 24 VAC output to one or more cameras.

A fuse inside the sealed unit provides protection against power supply or camera failure.



TF2000



MODEL	Α	В	С		
TF2000	2.36 (5.99)	2.98 (7.57)	1.91 (4.85)		
TF9000	2.75 (6.99)	3.10 (7.88)	2.20 (5.59)		

NOTE: VALUES IN PARENTHESES ARE CENTIMETERS; ALL OTHERS ARE INCHES.

# **TECHNICAL SPECIFICATIONS**

#### **MODELS**

TF2000 Indoor, camera power supply, 120 VAC input.

One fused, 24 VAC output, 20 VA

TF9000 Same as TF2000 except 50 VA output

#### **ELECTRICAL**

Input Voltage 120 VAC, 60 Hz Output Voltage 24 VAC

**Output Power** 

TF2000 20 VA TF9000 50 VA

Overload Protection Internal fuse (non-serviceable)

Input Connectors Two blades

Output Connectors Two screw terminals

Recommended Wiring Distances

See chart below

The following are the recommended maximum distances (transformer to load) and are calculated with a 10-percent voltage drop. (Ten percent is generally the maximum allowable voltage drop for AC-powered devices.) Distances are calculated in feet; values in parentheses are meters.

#### **Recommended Wiring Distance Chart**

			Wire Gauge						
Input		Total VA	20 AWG		18 AWG		16 AWG		
Voltag	е	Consumed	(0.5 mm <sup>2</sup> )		(1.0 mm <sup>2</sup> )		(1.5 mm <sup>2</sup> )		
24 VA(	3	10	283	(86)	451	(137)	716	(218)	
		20	141	(42)	225	(68)	358	(109)	
		50	56	(17)	90	(27)	143	(43)	

#### **GENERAL**

Construction Plastic
Finish Beige
Environment Indoor

Unit Weight

TF2000 0.80 lb (0.36 kg) TF9000 1.70 lb (0.76 kg)

Shipping Weight

TF2000 1 lb (0.45 kg) TF9000 2 lb (0.91 kg)

