Camclosure® 2 Series Mounts PENDANT, WALL, AND FLUSH MOUNTS

Product Features

- Specifically Designed to Compliment All Camclosure® 2 Series Camera Systems
- Indoor and Outdoor Use
- · Pendant Options for All Models
- Durable Aluminum Construction on IS50/IS51 Series Models
- IS50/IS51 Series is Compatible with Many Pelco Mounts
- Integrated Wall Mounts in IS20/IS21 Series
- Flush Mount Kits Available for All Models



IS50 SHOWN WITH
IS50-P PENDANT ADAPTER
AND SWM-SR WALL MOUNT

The **Camclosure® 2 Series** mounts offer versatile alternative mounting options for Pelco's Camclosure 2 Series camera systems when a surface or flush (in-ceiling) installation location is not available. These economical mounts are designed specifically for the Camclosure 2 Series, ensuring ease of installation and cohesion in the look of the Camclosure 2 lineup.

The **IS20 and IS20DWS Series** indoor mounts are available in pendant, wall, and flush models to complement any installation. All of the mounts are color matched and made from rugged ABS plastic, which is sonic welded for strength and designed with the installer in mind. The **IS20 and IS20DWS Series** mounts provide internal cable routing to conceal wiring. The pendant models are compatible with 3/4-inch and 25 mm conduit fittings, making them universal worldwide. The wall mount models attach easily to a solid surface or junction box using the supplied adapter plate. The flush mount kit modifies a surface mount camera for in-ceiling installations if the installation environment should change after the original deployment.

The **IS50 Series** outdoor mounts are available in pendant and flush models. The **IS50 Series** pendant is equipped with a 1.5-inch NPT thread for easy mounting. In addition, the pendant model can be paired with Pelco's SWM-SR for wall mount installations. The **IS50 Series** mounts are color matched, made from cast aluminum for strength and weather protection, and provide internal cable routing to conceal wiring.



TECHNICAL SPECIFICATIONS

PENDANT MOUNT FEATURES

IS20-P

- Pendant mount for IS20-CH and IS20-DN Series cameras
- Color matched ABS plastic construction
- Accepts 0.75-inch and 25 mm conduit fittings
- · Indoor use
- Provides an attractive mounting alternative when surface or flush mounting is not available

IS20DWS-P


- Pendant mount for IS20-DWS Series cameras
- Color matched ABS plastic construction
- Accepts 0.75-inch and 25 mm conduit fittings
- Indoor use
- Provides an attractive mounting alternative when surface or flush mounting is not available

IS50-P

- Pendant mount for all IS50 Series cameras
- Durable all-aluminum construction
- 1.5-inch NPT thread for easy adaptation to any environment or Pelco mount
- Rugged/outdoor use
- Provides an attractive mounting alternative when surface or flush mounting is not available








Ø 5.10 (12.95)

2.07 (5.26)






WALL MOUNT FEATURES

IS20-WM

- Integrated wall mount for IS20-CH and IS20-DN Series cameras
- Color matched ABS plastic construction
- Mounts to a flat wall
- Indoor use
- Internal cable pass for a neat installation
- Junction box adapter included






IS20DWS-WM

- Integrated wall mount for IS20-DWS Series cameras
- Color matched ABS plastic construction
- Mounts to a flat wall
- Indoor use
- Internal cable pass for a neat installation
- Junction box adapter included






TECHNICAL SPECIFICATIONS

FLUSH KIT FEATURES

IS20-FK

- Adapts IS20-CH and IS20-DN Series surface mount cameras for flush (in-ceiling) applications
- Durable constructionEasy to install
- Color matched trim ring included






IS20DWS-FK

- Adapts IS20-DWS Series surface mount cameras for flush (in-ceiling) applications
- Indoor use
- Durable construction
- Easy to install
- Color matched trim ring included






IS50-FK

- Adapts all IS50 Series surface mount cameras for flush (in-ceiling) applications
- Indoor use or weather-protected outdoor use
- Durable construction
- Easy to install
- Color matched trim ring included





NOTE: VALUES IN PARENTHESES ARE CENTIMETERS; ALL OTHERS ARE INCHES.

TECHNICAL SPECIFICATIONS

IS20-CH/IS20-DN CAMCLOSURE 2 SERIES

MODELS

IS20-P Pendant mount adapter
IS20-WM Wall mount adapter
IS20-FK Flush mount kit

MECHANICAL

Suggested Mounting Method

IS20-P Attach to a mount using 3/4-inch NPT or

25 mm conduit fitting

IS20-WM Install the adapter plate (supplied) on a wall

or junction box using appropriate hardware; attach wall mount to adapter plate; attach the camera with hardware supplied with mount

IS20-FK Use the template (supplied) to cut a mounting

hole; secure the flush kit with the attached spring hooks and clamping screws; attach the camera with four fixing screws (supplied); secure the flush mount cover with the

attached spring hooks

GENERAL

Construction

IS20-P ABS plastic IS20-WM ABS plastic IS20-FK Steel and ABS plastic

Finish White

 Weight
 Unit
 Shipping

 IS20-P
 0.20 lb (0.09 kg)
 1 lb (0.45 kg)

 IS20-WM
 0.62 lb (0.28 kg)
 2 lb (0.90 kg)

 IS20-FK
 0.62 lb (0.28 kg)
 2 lb (0.90 kg)

IS20-DWS CAMCLOSURE 2 SERIES

MODELS

IS20DWS-P Pendant mount adapter
IS20DWS-WM Wall mount adapter
IS20DWS-FK Flush mount kit

MECHANICAL

Suggested Mounting Method

IS20DWS-P Attach using 3/4-inch NPT or 25 mm conduit

fitting

IS20DWS-WM Install adapter plate (supplied) on wall or

junction box using appropriate hardware; attach wall mount to adapter plate; attach camera with hardware supplied with mount

IS20DWS-FK Use the template (supplied) to cut a mounting

hole; install two M10 anchor bolts (not supplied) into the ceiling; attach the flush mount kit using the safety chain (supplied) and hardware (supplied); mount the camera and attach the flush mount cover

GENERAL

Construction

IS20DWS-P ABS plastic IS20DWS-WM ABS plastic IS20DWS-FK Steel and ABS plastic

Finish White

 Weight
 Unit
 Shipping

 IS20DWS-P
 0.22 lb (0.10 kg)
 1 lb (0.45 kg)

 IS20DWS-WM
 0.64 lb (0.29 kg)
 2 lb (0.90 kg)

 IS20DWS-FK
 1.61 lb (0.73 kg)
 4 lb (1.47 kg)

IS50 CAMCLOSURE 2 SERIES

MODELS

IS50-P Pendant mount adapter

(can be paired with SWM-SR for wall mount

applications)

IS50-FK Flush mount kit

MECHANICAL

Suggested Mounting Method

IS50-P Attach to a mount using 1.5-inch NPT male

hreads

IS50-FK Use the template (supplied) to cut a mounting

hole; install two M10 anchor bolts (not supplied) into the ceiling; attach the flush mount kit using the safety chain (supplied) and hardware (supplied); mount the camera and attach the flush mount cover (supplied)

GENERAL

Construction IS50-P

IS50-P Cast aluminum IS50-FK Steel and ABS plastic

Finish

IS50-P Powder coat, light gray

IS50-FK Light gray

 Weight
 Unit
 Shipping

 IS50-P
 0.76 lb (0.34 kg)
 2 lb (0.90 kg)

 IS50-FK
 1.54 lb (0.70 kg)
 4 lb (1.44 kg)

OPTIONAL MOUNT ADAPTER

SWM-SR

Compact wall mount, light gray finish. Can be used with IS50-P for wall-mount installations. Can also be adapted for corner or pole

applications.