



MAN BOON MANUFACTORY LTD.

PRODUCT TECHNICAL DATA SHEET

Product Code: **T9504-LSNH**

Page: **1 of 1**

Part Number : **20120522-22** Version: **A0**


Date: **2012-5-22**

Dimensional Features		Material Breakdown
Inner Conductor <A>	8 / T0.20(+/-0.008)mm×7	Stranded Tinned copper
Insulation	8 / 1.10(+/-0.13)mm	SPE Insulation (white,green,red,blue,black×4)
Shield <C>	Al-foil	Al-foil Shield
Drain <D>	T0.20(+/-0.008)mm×7	Stranded Tinned copper
Sheath<E>	6.73 (+/-0.25)mm	Grey LSNH Sheath

Electrical Characteristics

Max.Conductor(A) DC Resistance at 20°C(Ω/100M)	<9.41
Min.Insulation DC Resistance at 20°C (MΩ*M)	>200
Rated Temperature(°C)	80
Rated Voltage (V)	300

Cable Construction



Physical Characteristics

Minimum Bending Radius(mm)	15×D
Conductor Elongation at Break(%)	>10.0%
Sheath Tensile Strength (N/mm ²)	10.00
Sheath Elongation at Break(%)	100.0%

Remark: Please contact us if you have more requirements or specifications subject to change,or else in accordance with the standards.

Please note that the above specification is based on the received requirements and/or our design, we reserve the right to update it to reflect the latest changes



Man Boon Manufactory Ltd.
Unit 11, 5/F, Wing On Plaza, 62 Mody Road, Tsim Sha Tsui, Kowloon, Hong Kong
Tel: 852- 2558 7578 Fax: 852- 28970314
email: info@manboon.com www.manboon.com



ISO 9001
File A8606

RoHS (2002/95/EC)
Compliant