



40417

Nylon Cable Tie, 14.25 in length

Dimensions

Nominal Size	1/2 in 1/4 in 3/8 in
Compatible Diameter, maximum	16.510 mm 0.650 in
Compatible Diameter, minimum	10.414 mm 0.410 in
Height	0.00 mm 0.00 in
Length	361.95 mm 14.25 in
Width	4.57 mm 0.18 in

General Specifications

Hanger Type	Cable tie
Color	Black
Material Type	Engineered plastic
Package Quantity	50

Mechanical Specifications

Mounting	Angle member Cable ladder Round member
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Tensile Strength	83 N/mm ² 12000 psi

Packed Dimensions

Length	37.8 cm 14.9 in
Shipping Weight	0.35 kg 0.77 lb
Width	12.2 cm 4.8 in

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
China RoHS SJ/T 11364-2006	Below Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Tensile Strength	Tensile Strength at 73° F
------------------	---------------------------