



## SFX-DM-20

**SFX-500 Jumper with interface type 7-16 DIN Male, 20 ft**

### General Specifications

|                         |                     |
|-------------------------|---------------------|
| Body Style, Connector A | Straight            |
| Cable Family            | SFX-500             |
| Interface, Connector A  | 7-16 DIN Male       |
| Interface, Connector B  | Sold separately     |
| Length                  | 6.096 m   20.000 ft |
| Attachment, Connector A | Factory attached    |
| Attachment, Connector B | Factory attached    |

### Electrical Specifications

|                  |           |
|------------------|-----------|
| DTF, Connector A | -34.00 dB |
|------------------|-----------|

### Jumper Assembly Sample Label



### Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz    | 1.06 | 30.70            |
| 1700–2200 MHz  | 1.09 | 27.32            |
| 2200–2500 MHz  | 1.10 | 26.44            |

### Regulatory Compliance/Certifications

| Agency        | Classification                                                                 |
|---------------|--------------------------------------------------------------------------------|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

### Included Products

SFX-500 — SFX-500, HELIAX® Superflexible Coaxial Cable, smoothwall aluminum, 1/2 in, black PE jacket

SFX-ADM — 7-16 DIN Male for 1/2 in SFX-500 cable