



SFX-DM-6

SFX-500 Jumper with interface type 7-16 DIN Male, 6 ft

General Specifications

Body Style, Connector A	Straight
Cable Family	SFX-500
Interface, Connector A	7-16 DIN Male
Interface, Connector B	Sold separately
Length	1.829 m 6.000 ft
Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached

Electrical Specifications

DTF, Connector A	-34.00 dB
------------------	-----------

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.06	30.70
1700–2200 MHz	1.09	27.32
2200–2500 MHz	1.10	26.44

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

SFX-500 — SFX-500, HELIAX® Superflexible Coaxial Cable, smoothwall aluminum, 1/2 in, black PE jacket

SFX-ADM — 7-16 DIN Male for 1/2 in SFX-500 cable