



SFX-DMNM-30

SFX-500 Jumper with interface types 7-16 DIN Male and N Male, 30 ft

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	SFX-500
Interface, Connector A	7-16 DIN Male
Interface, Connector B	N Male
Length	9.144 m 30.000 ft
Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached

Electrical Specifications

DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.06	30.70
1700–2200 MHz	1.10	26.44
2200–2500 MHz	1.10	26.44

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

SFX-500 — SFX-500, HELIAX® Superflexible Coaxial Cable, smoothwall aluminum, 1/2 in, black PE jacket

SFX-ANM — Type N Male A Series for 1/2 in SFX-500 cable

SFX-ADM — 7-16 DIN Male for 1/2 in SFX-500 cable