



## TFAM17/19-34

**ION™-B Series Medium Power Remote Unit for AWS and PCS 1900**

### General Specifications

Power Type	Medium
Brand	ION™-B
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.

### Electrical Specifications

License Band	AWS   PCS 1900
Voltage Range	-60 to -36 Vdc

### Electrical Specifications Rx (Uplink)

Operating Frequency Band 1710 – 1755 MHz (AWS) | 1850 – 1910 MHz (PCS 1900)

### Electrical Specifications Tx (Downlink)

Operating Frequency Band 1930 – 1990 MHz (PCS 1900) | 2110 – 2155 MHz (AWS)

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### Included Products

TPSN3/05-30 — Power Supply Adapter ION™-B Series Remote Units, 30 W