



TFAM80/92/19EP-34

ION™-B Series Medium Power Remote Unit for LMR 800, LMR 900, and Extended PCS 1900

Replaced By:

TFAH-US7B-34

ION™-B Series High Power Remote Unit for Cellular 700, LMR 800, Cellular 850, LMR 900, AWS, PCS 1900, and WiMAX

General Specifications

Power Type	Medium
Brand	ION™-B
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.

Electrical Specifications

License Band	LMR 800 LMR 900 PCS 1900 Extended
Voltage Range	-60 to -36 Vdc

Electrical Specifications Rx (Uplink)

Operating Frequency Band	1850 – 1915 MHz (PCS 1900 Extended) 806 – 824 MHz (LMR 800) 896 – 902 MHz (LMR 900)
--------------------------	---

Electrical Specifications Tx (Downlink)

Operating Frequency Band	1930 – 1995 MHz (PCS 1900 Extended) 851 – 869 MHz (LMR 800) 935 – 941 MHz (LMR 900)
--------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

TPSN3/28-80 — Power Supply Adapter ION™-B Series Remote Units, 80 W