



XP-3040

Crossover Plate, joins 3-1/2 in to 4-1/2 in OD round members

Dimensions

Mounting Diameter, maximum	114.3 mm		4 1/2 in
Mounting Diameter, minimum	88.9 mm		3 1/2 in
Height	127.0 mm		5.0 in
Length	304.8 mm		12.0 in
Weight	6.5 kg		14.3 lb
Width	254.0 mm		10.0 in

General Specifications

Product Type	Clamp sets
Tower Taper	Non-tapered
Includes	Plates U-bolts
Material Type	Hot dip galvanized steel
Mounting	Crossover plate
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system