



106664147 | M30MC-262  
Rectangular Mounting Collar, white

## Dimensions

|        |          |  |         |
|--------|----------|--|---------|
| Depth  | 11.68 mm |  | 0.46 in |
| Height | 25.40 mm |  | 1.00 in |
| Weight | 0.00 kg  |  | 0.01 lb |
| Width  | 26.16 mm |  | 1.03 in |

## Environmental Specifications

|                 |     |  |    |
|-----------------|-----|--|----|
| Safety Standard | cUL |  | UL |
|-----------------|-----|--|----|

## General Specifications

|                       |                                |
|-----------------------|--------------------------------|
| Color                 | White                          |
| Mount Type            | Snap-in                        |
| Total Ports, quantity | 1                              |
| Product Type          | Mounting collar                |
| Application           | Fit into a rectangular opening |
| Package, quantity     | 100                            |

## Mechanical Specifications

|               |                                                              |
|---------------|--------------------------------------------------------------|
| Material Type | High-impact, flame retardant, UL-rated 94 V-0, thermoplastic |
|---------------|--------------------------------------------------------------|

## Regulatory Compliance/Certifications

|               |                                                                                |
|---------------|--------------------------------------------------------------------------------|
| <b>Agency</b> | <b>Classification</b>                                                          |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |