



107765992 | 2010B WH 25/24 R1000

CommScope® 2010B Category 3 U/UTP Cable, plenum, white jacket, 25 pair count, 1000 ft (305 m) length, reel

Construction Materials

Conductor Material	Bare copper
Insulation Material	PVC
Jacket Material	PVC

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	119.00 lb/kft
Diameter Over Jacket	9.779 mm 0.385 in
Jacket Thickness	0.508 mm 0.020 in

Electrical Specifications

ANSI/TIA Category	3
Characteristic Impedance	100 ohm
Characteristic Impedance Tolerance	±15 ohm
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Mutual Capacitance	6.6 nF/100 m @ 1 kHz
Operating Frequency, maximum	16 MHz
Transmission Standards	ANSI/TIA-568-C.2
Safety Voltage Rating	300 V
Dielectric Strength, minimum	1500 Vac 2500 Vdc

Environmental Specifications

Environmental Space	Plenum
Flame Test Method	CMP
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Smoke Test Method	CMP

General Specifications

Brand	CommScope®
Cable Component Type	Backbone
Cable Type	U/UTP (unshielded)
Pairs, quantity	25
Jacket Color	White
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid

Product Specifications



107765992 | 2010B WH 25/24 R1000

Conductors, quantity	50
Packaging Type	Reel
Product Number	2010B

Mechanical Specifications

Pulling Tension, maximum	68 kg 150 lb
--------------------------	----------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

