



760082545 | RK4P45-29S

**29 in (737 mm) D x 7 ft (2134 mm) H - 19 in (482.6 mm) Steel Equipment Rack (45U)  
3/8 Sq Punch, Black**

## Dimensions

Channel Width	3.0 in
Depth	1041.4 mm   41.0 in
Dimensional Standards	EIA-310-E
Height	2133.6 mm   84.0 in
Weight	47.63 kg   105.00 lb
Width	518.2 mm   20.4 in

## Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

## General Specifications

Product Type	4 post rack
Rack Units	45
Color	Black
Finish	Powder-coated, textured
Includes	Base pan   Forty #12-24 x 1/2 in mounting screws   Forty M6 cage nuts   Four vertical rack rails   Instruction sheet   Twelve 3/8 in split lock washers   Twelve 3/8 -16 hex nuts   Twelve 3/8-16 UNC x 1 in hex head bolts   Two extruded base angles   Two extruded top angles   Upper plate support
Package, quantity	1
Packaging Type	Flat packed
Rack Type	EIA 19 in

## Mechanical Specifications

Rail Mounting Hole	3/8 in
Material Type	Steel
Static Load Rating	907.2 kg   2000.0 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

# Product Specifications

COMMSCOPE®

760082545 | RK4P45-29S

