



760083600 | PSV5-15SP-CBSP

Vertical Power Distribution Strip, 125V, 15A, Surge Protected, with Circuit Breaker, Standard plug

Dimensions

Cable Length	3.0 m 10.0 ft
Depth	41.0 mm 1.6 in
Height	41.0 mm 1.6 in
Width	1683.0 mm 66.3 in
Weight	5.00 kg 11.02 lb

Electrical Specifications

Current	15.00 A
Overcurrent Protection	15 A
Circuit Breaker	Yes
On/Off Switch	No
Plug Standard	NEMA L5-15P, straight blade
Power Frequency	50/60 Hz
Power Rating, maximum	1.40 kW
Receptacle Standard	NEMA 5-15R
Surge Indicator	Yes
Surge Protection	Yes
Voltage	125 V

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Product Type	Vertical power strip
Color	Black
Finish	Powder-coated, textured
Includes	Instruction sheet Plastic bottom mounting clip Two #10 -32 x 1/2 in panhead screws Two plastic top mounting clips Vertical PDU
Package, quantity	1
Receptacle, quantity	20

Mechanical Specifications

Material Type	Steel
---------------	-------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

760083600 | PSV5-15SP-CBSP

