

## 760083790 | PSH5-15NP-NBSP

**Horizontal Power Distribution Strip, 125V, 15A, No Surge Protection, No Circuit Breaker, Standard plug**

### Dimensions

Cable Length	3.0 m   10.0 ft
Depth	41.0 mm   1.6 in
Height	41.0 mm   1.6 in
Width	432.0 mm   17.0 in
Weight	3.00 kg   6.61 lb

### Electrical Specifications

Current	15.00 A
Overcurrent Protection	No protection
Circuit Breaker	No
On/Off Switch	No
Plug Standard	NEMA L5-15P, straight blade
Power Frequency	50/60 Hz
Power Rating, maximum	1.40 kW
Receptacle Standard	NEMA 5-15R
Surge Indicator	No
Surge Protection	No
Voltage	125 V

### Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

### General Specifications

Product Type	Horizontal power strip
Color	Black
Finish	Powder-coated, textured
Includes	Horizontal PDU   Instruction sheet   Two pre-mounted metal brackets
Package, quantity	1
Receptacle, quantity	8

### Mechanical Specifications

Material Type	Steel
---------------	-------

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

# Product Specifications

COMMScope®

760083790 | PSH5-15NP-NBSP

