



760090159 | RK12-45S

12 in (305 mm) Channel x 7ft (2135 mm) H - 19 in (482.6 mm) Steel Equipment Rack (45U) 3/8 Sq Punch, Black

Dimensions

Channel Width	12.0 in
Depth	609.6 mm 24.0 in
Dimensional Standards	EIA-310-E
Height	2133.6 mm 84.0 in
Weight	25.40 kg 56.00 lb
Width	518.2 mm 20.4 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Product Type	2 post rack
Rack Units	45
Color	Black
Finish	Powder-coated, textured
Includes	Forty #12-24 x 1/2 in mounting screws Forty M6 cage nuts Instruction sheet Twelve 3/8 in split lock washers Twelve 3/8 -16 hex nuts Twelve 3/8 -16 UNC x 1 in hex head bolts Two extruded base angles Two extruded top angles Two vertical rack rails
Package, quantity	1
Packaging Type	Flat packed
Rack Type	EIA 19 in

Mechanical Specifications

Rail Mounting Hole	3/8 in
Material Type	Steel
Static Load Rating	453.6 kg 1000.0 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

