



760095737 | CW26-PVF-24

Wall Mount Cabinet, 48 in (1219 mm) H (26U), Plexiglass Door, Vented Sides, 2 Fans, 24 in (610 mm) Deep, 12-24 Tapped Rails

Dimensions

Height	1219.2 mm 48.0 in
Depth	609.6 mm 24.0 in
Dimensional Standards	EIA-310-E
Weight	34.02 kg 75.00 lb
Width	584.2 mm 23.0 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Rack Units	26
Color	Black
Finish	Powder-coated, hammertone
Includes	Instruction sheet Twenty #12 -24 x 1/2 in mounting screws Two 115 V fans Wall mount cabinet
Package, quantity	1
Packaging Type	Assembled

Mechanical Specifications

Door Material, front	Plexiglass
Side Panel Vent	Vented
Top Panel Vent	Vented/Perforated
Static Load Rating	56.7 kg 125.0 lb
Bottom Panel	Included
Bottom Panel Vent	Vented
Cable Entry, bottom	Two 1 in diameter openings Two 3 in diameter openings
Cable Entry, top	Two openings of 1 in diameter Two 3 in diameter openings
Door Type, front	Single
Door Vent, front	Solid
Material Type	Steel
Side Panels	Included
Top Panel	Included

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

760095737 | CW26-PVF-24



Included Products

760096099 | CWFK2-120 — Fan Kit, 2 Fans, 120VAC