



## 760118026 | MFC-STF-09-6X

**OptiSPEED® Fiber Qwik II-ST Connector™, field installable, beige**

### Construction Materials

Fiber Type	OptiSPEED®, 62.5 µm multimode fiber
Ferrule Geometry	Factory polished
Ferrule Material	Zirconia

### Dimensions

Compatible Cable Diameter	0.9 mm   0.0 in
Length	50.2 mm   2.0 in

### General Specifications

Interface	ST
Body Style	BTW
Interface Feature	Field Installable
Color	Beige
Package, quantity	1

### Mechanical Specifications

Cable Retention Strength, maximum	0.23 kg @ 0 ° 0.50 lb @ 0 °
-----------------------------------	--------------------------------

### Optical Performance

Insertion Loss, typical	0.40 dB
Return Loss, minimum	20.0 dB
Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB

### Optical Specifications

Optical Components Standard	ANSI/TIA-568-C.3
-----------------------------	------------------

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

---

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from 0 °C to +60 °C (+32 °F to +140 °F)