



## 760145060 | PDU-1U-12xC13-OUT-3M-SCH-EMEA

**Horizontal Power Distribution Strip, 230V, 16A, No Surge Protection, No Circuit Breaker, 1U x 19 in 12 x C13 out - 3M Schuko Plug**

### Dimensions

Cable Length	3.0 m   9.8 ft
Depth	45.0 mm   1.8 in
Height	41.0 mm   1.6 in
Width	482.6 mm   19.0 in

### Electrical Specifications

Current	16.00 A
Overcurrent Protection	No protection
Circuit Breaker	No
On/Off Switch	No
Plug Standard	CEE 7/4 (Schuko)
Power Frequency	50/60 Hz
Power Rating, maximum	3.68 kW
Receptacle Standard	IEC Type C-13
Surge Indicator	No
Surge Protection	No
Voltage	230 V

### Environmental Specifications

Safety Standard	CE
-----------------	----

### General Specifications

Product Type	Horizontal power strip, 19 in, mounted
Color	Black
Finish	Powder-coated, textured
Includes	Two mounting brackets
Ordering Note	Available in Europe, the Middle East, and Africa
Package, quantity	1
Receptacle, quantity	12

### Mechanical Specifications

Material Type	Steel
---------------	-------

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

# Product Specifications



760145060 | PDU-1U-12xC13-OUT-3M-SCH-EMEA

