



760162040 | SHELF-ADJ-19-1U-24X36  
Shelf, Adj, 19"x1Ux24-36D, 125# AI

## Dimensions

Dimensional Standards	EIA-310-D
Height	1.7 in   43.7 mm
Width	19.0 in   482.6 mm
Depth	24.0 in   610.0 mm
Adjustable Depth, maximum	36.0 in   914.0 mm

## General Specifications

Product Type	Shelf
Rack Units	1
Color	Black
Finish	Powder-coated, textured
Includes	Eight #10-32 pan head screws   Eight #12 -24 x 1/2 in mounting screws   Eight KEPS nuts   Fixed shelf
Package, quantity	1
Rack Type	EIA 19 in

## Mechanical Specifications

Material Type	Steel
Static Load Rating	125.0 lb   57.0 kg

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

