



CC0048215/1 | 350-1P-48P
Uniprise® Voice Grade Patch Panel, 48 port

Dimensions

Depth	44.45 mm 1.75 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	3
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	Uniprise®
Cable Type	U/UTP (unshielded)
Modules, quantity	1
Product Type	Panel
Total Ports, quantity	48
Color	Black
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	2

Mechanical Specifications

Panel Style	Straight
Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf 133 N
Rear Termination Type	RJ21

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

