

107655193 | M14MMO-270

MMO Type Flush Mounted Angled Faceplate, four port gray

Dimensions

Depth	32.77 mm 1.29 in
Height	144.53 mm 5.69 in
Weight	0.16 kg 0.36 lb
Width	83.31 mm 3.28 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Color	Gray
Mount Type	Flush
Total Ports, quantity	4
Product Type	Flush mount outlet
Application	has 45 degree angular ports for fiber and copper connectors
Package, quantity	1

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system