



## 760005256 | M81-SVHS-110-003

**S-Video to 110 Punchdown Module, black**

### Electrical Specifications

Attenuation dc, maximum	2 dB @ 5.5 MHz
Crosstalk	-60 dB @ 5.5 MHz
Impedance	75 ohm
Insulation Resistance, minimum	50 MOhm
UTP 110 Terminal Block	110 ohm

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Product Type	Multimedia outlet
Color	Black
Mount Type	Snap-in
Package, quantity	1

### Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

