



760105163 | 360-iP-G2-1U-LC-FX
SYSTIMAX 360™ iPatch® G2 LC Fiber Shelf, fixed

Dimensions

Depth	323.85 mm 12.75 in
Height	44.45 mm 1.75 in
Weight	1.81 kg 4.00 lb
Width	482.60 mm 19.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Intelligent fiber shelf
Body Style	Duplex
Color	Black
Interface	LC
Package, quantity	1
Shelf Movement	Fixed
Total Ports, quantity	24

Mechanical Specifications

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber LazrSPEED® 300, 50 µm multimode fiber LazrSPEED® 550, 50 µm multimode fiber OptiSPEED®, 62.5 µm multimode fiber TeraSPEED®, zero water peak singlemode fiber
Material Type	ABS Polycarbonate

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

