



760105486 | MGS-CAP-10
MGS Cap Kit - LP (Pack of 10)

Electrical Specifications

ANSI/TIA Category 6 | 6A

Environmental Specifications

Flammability Rating UL 94 V-0
Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity Up to 95%, non-condensing
Safety Standard cUL | UL
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand GigaSPEED® X10D | GigaSPEED® XL | SYSTIMAX®
Product Type Cap
Color Gray
Package, quantity 10

Mechanical Specifications

Material Type High-impact, flame retardant, thermoplastic

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

