Product Specifications

COMMSCOPE®

760116178 | 360DM-24LC-LS-6PK

InstaPATCH® 360 360DM-24LC-LS Module, 6-Pack

Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Total Fibers, quantity	24

Dimensions

Depth	116.8 mm | 4.6 in
Height	30.48 mm | 1.20 in
Width	91.4 mm | 3.6 in

Environmental Specifications

Safety Standard	UL

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Standard
Color, front	Aqua
Brand	InstaPATCH® 360
Interface, rear	MPO
Adapters, quantity, rear	2
Interface Feature, rear	Reduced footprint
Color, rear	Gray
Package, quantity	6

Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	0.50 dB
Return Loss, minimum	20.0 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

RoHS COMPLIANT

* Footnotes

©2012 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 19, 2012

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from 0 °C to +60 °C (+32 °F to +140 °F)

©2012 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 19, 2012