



760152306 | 360-iP-UP-KIT-PMAX-2U-24

SYSTIMAX 360™ iPatch® Upgrade Kit for PATCHMAX Panel, 2U, 24 Port, 10 pack

Dimensions

Depth	12.70 mm 0.50 in
Height	31.75 mm 1.25 in
Weight	0.11 kg 0.25 lb
Width	393.70 mm 15.50 in

Electrical Specifications

ANSI/TIA Category	6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Intelligent copper panel
Color	Cool gray
Package, quantity	10
Total Ports, quantity	24

Mechanical Specifications

Material Type	ABS Polycarbonate
---------------	---------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

