



760152363 | 360-iP-1100-E-GS6-1U-24  
**SYSTIMAX 360™ iPatch® 1100GS6 Evolve U/UTP Patch Panel, 24 port**

## Dimensions

|                                   |                      |
|-----------------------------------|----------------------|
| Depth                             | 38.10 mm   1.50 in   |
| Diameter Over Dielectric, maximum | 1.168 mm   0.046 in  |
| Diameter Over Dielectric, minimum | 0.762 mm   0.030 in  |
| Height                            | 44.45 mm   1.75 in   |
| Weight                            | 0.73 kg   1.60 lb    |
| Width                             | 482.60 mm   19.00 in |

## Electrical Specifications

|                                                       |                                |
|-------------------------------------------------------|--------------------------------|
| ANSI/TIA Category                                     | 6A                             |
| Current Rating                                        | 1.5 A @ 20 °C<br>1.5 A @ 68 °F |
| Dielectric Withstand Voltage, RMS, conductive surface | 1500 Vac @ 60 Hz               |
| Dielectric Withstand Voltage, RMS, contact-to-contact | 1000 Vac @ 60 Hz               |
| Insulation Resistance, minimum                        | 500 MOhm                       |

## Environmental Specifications

|                       |                                      |
|-----------------------|--------------------------------------|
| Flammability Rating   | UL 94 V-0                            |
| Operating Temperature | -5 °C to +50 °C (+23 °F to +122 °F)  |
| Relative Humidity     | Up to 95%, non-condensing            |
| Safety Standard       | Austel   CE   CSA   UL               |
| Storage Temperature   | -40 °C to +70 °C (-40 °F to +158 °F) |

## General Specifications

|                       |                                                                                                                             |
|-----------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Brand                 | iPatch®   SYSTIMAX 360™   SYSTIMAX®                                                                                         |
| Product Type          | Intelligent copper panel                                                                                                    |
| Color                 | Cool gray                                                                                                                   |
| Includes              | Cable management bar   Four "A" labels   Four #12 -24 mounting screws   Instruction sheet   Panel   Twenty -four cable ties |
| Intelligence Type     | iPatch® enabled                                                                                                             |
| Package, quantity     | 1                                                                                                                           |
| Total Ports, quantity | 24                                                                                                                          |

## Mechanical Specifications

|                                |                            |
|--------------------------------|----------------------------|
| Panel Style                    | Straight                   |
| Material Type                  | ABS   Polycarbonate        |
| Outlet/Module Contact Plating  | Precious metals            |
| Plug Insertion Life, minimum   | 750 times                  |
| Plug Insertion Life, test plug | IEC 60603-7 compliant plug |
| Plug Retention Force, minimum  | 133 N   30 lbf             |

760152363 | 360-iP-1100-E-GS6-1U-24

Wiring T568A | T568B

## Regulatory Compliance/Certifications

| Agency          | Classification                                                                 |
|-----------------|--------------------------------------------------------------------------------|
| RoHS 2002/95/EC | Compliant                                                                      |
| ISO 9001:2008   | Designed, manufactured and/or distributed under this quality management system |

