



760158618 | 360-iP-UP-KIT-AE-48

SYSTIMAX 360™ iPatch® Upgrade Kit for Evolve Angled Panel, 48 Port, 5 pack

Dimensions

Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Weight	0.11 kg 0.25 lb

Electrical Specifications

ANSI/TIA Category	6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Intelligent copper panel
Color	Cool gray
Package, quantity	5
Total Ports, quantity	48

Mechanical Specifications

Material Type	ABS Polycarbonate
---------------	---------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

