



760158626 | 360-iP-1100A-E-GS3-1U-24

SYSTIMAX 360™ iPatch® 1100GS3 Evolve U/UTP Angled Patch Panel, 24 port

Dimensions

Depth	266.70 mm 10.50 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	44.45 mm 1.75 in
Weight	0.82 kg 1.80 lb
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Intelligent copper panel
Color	Cool gray
Includes	Cable management bar Four "A" labels Four #12 -24 mounting screws Instruction sheet Panel Twenty -four cable ties
Intelligence Type	iPatch® enabled
Package, quantity	1
Total Ports, quantity	24

Mechanical Specifications

Panel Style	Angled
Material Type	ABS Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	133 N 30 lbf

760158626 | 360-iP-1100A-EGS3-1U-24

Wiring T568A | T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

