



## CPC3312-08 | GS8E-WH

**GigaSPEED® XL GS8E Stranded Cordage Modular Patch Cord, White Jacket**

### Dimensions

Cord Length, maximum	30 m   100 ft
Cord Length, minimum	1 m   1 ft

### Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

### Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	Anatel   cETL   ETL

### General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	White
Brand	GigaSPEED® XL   SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

### Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

### Wiring Diagram



## Regulatory Compliance/Certifications

---

**Agency**

RoHS 2002/95/EC  
ISO 9001:2008

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

---

860125558 | 1074E WH 4/24 RVAR (Product Component—not orderable) — GigaSPEED® XL 1074E Category 6 U/UTP Cable, non-plenum, white jacket, 4 pair count, variable length, reel