



## CPC3482-09 | GS8E117-S-YL

**GigaSPEED® XL GS8E Single End Solid Cable Modular Patch Cord, Yellow Jacket**

### Dimensions

Cord Length, maximum	100 m   300 ft
Cord Length, minimum	1 m   1 ft

### Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

### Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	Unterminated
Jacket Color	Yellow
Brand	GigaSPEED® XL   SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

### Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

### Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	
Position 2	Orange	
Position 3	Lt. Green	
Position 4	Blue	
Position 5	Lt. Blue	
Position 6	Green	
Position 7	Lt. Brown	
Position 8	Brown	

## Regulatory Compliance/Certifications

### Agency

RoHS 2002/95/EC  
ISO 9001:2008

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

860062702 | 1071E YL 4/23 RVAR (Product Component—not orderable) — GigaSPEED® XL 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, yellow jacket, 4 pair count, variable length, reel