



## CPC5311-03 | VP119-P8GS-A-DG

**GigaSPEED® XL VisiPatch® to GS8E 4-pair Hybrid Patch Cord A-wired, Dark Gray Jacket**

### Dimensions

Cord Length, maximum	30 m   100 ft
Cord Length, minimum	1 m   1 ft

### Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm

### Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

Interface, connector A	VisiPatch®
Interface, connector B	RJ45 plug
Product Type	Cord
Brand	SYSTIMAX®   VisiPatch®
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray
Package, quantity	1
Pairs, quantity	4

### Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N   10 lbf
Wiring	T568A

### Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	White/Orange
Position 2	Blue	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Green	Blue
Position 5	White/Orange	Lt. Blue
Position 6	Orange	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Regulatory Compliance/Certifications

**Agency**

RoHS 2002/95/EC  
ISO 9001:2008

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

860017029 | 1074E DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED® XL 1074E Category 6 U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel