



CPC5513-07 | VP-P8GS-X3-RD

GigaSPEED® XL VisiPatch® to VisiPatch® 4-pair Patch Cord Crossover, Red Jacket

Dimensions

Cord Length, maximum	30 m 100 ft
Cord Length, minimum	1 m 1 ft

Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Interface, connector A	VisiPatch®
Interface, connector B	VisiPatch®
Product Type	Cord
Brand	SYSTIMAX® VisiPatch®
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Red
Package, quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N 10 lbf
Wiring	VisiPatch® crossover

Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	Lt. Brown
Position 2	Blue	Brown
Position 3	White/Orange	Lt. Green
Position 4	Orange	Green
Position 5	Lt. Green	White/Orange
Position 6	Green	Orange
Position 7	Lt. Brown	Lt. Blue
Position 8	Brown	Blue

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

860018639 | 1074E RD 4/24 RVAR (Product Component—not orderable) — GigaSPEED® XL 1074E Category 6 U/UTP Cable, non-plenum, red jacket, 4 pair count, variable length, reel