



CPC5662-03 | VP119-P2PS-DG

VisiPatch® to PowerSUM D8PS 1 Pair Hybrid Patch Cord, Dark Gray Jacket

Dimensions

Cord Length, maximum	30 m 100 ft
Cord Length, minimum	1 m 1 ft

Electrical Specifications

ANSI/TIA Category	5e
dc Resistance, maximum	0.30 ohm

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Interface, connector A	VisiPatch®
Interface, connector B	RJ45 plug
Product Type	Cord
Brand	SYSTIMAX® VisiPatch®
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray
Package, quantity	1
Pairs, quantity	1

Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	18 N 4 lbf
Wiring	VisiPatch®

Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	
Position 2	Blue	
Position 3		
Position 4		Blue
Position 5		Lt. Blue
Position 6		
Position 7		
Position 8		

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

848202800 | 1074C DG 1/24 RVAR (Product Component—not orderable) — GigaSPEED® XL 1074C Category 5e U/UTP Cable, non-plenum, dark gray jacket, 1 pair count, variable length, reel