



CPCSSX2-06 | 360GS10E-OR

GigaSPEED® X10D 360GS10E Solid Cordage Modular Patch Cord, Orange Jacket

Dimensions

Cord Length, maximum	100 ft 30 m
Cord Length, minimum	1 m 3 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Orange
Brand	GigaSPEED® X10D SYSTIMAX 360™ SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N 30 lbf
Wiring	T568B

Wiring Diagram



CPCSSX2-06 | 360GS10E-OR

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

860474303 | 1095B OR 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, orange jacket, 4 pair count, variable length, reel