

**CPCSSY2-0Z | 360GS10E-P-BL****GigaSPEED® X10D 360GS10E Solid Plenum Cordage Modular Patch Cord, Blue Jacket**

## Dimensions

Cord Length, maximum	30 m   100 ft
Cord Length, minimum	1 m   3 ft

## Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

## Environmental Specifications

Environmental Space	Plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

## General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Blue
Brand	GigaSPEED® X10D   SYSTIMAX 360™   SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

## Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

## Wiring Diagram



CPCSSY2-0Z | 360GS10E-P-BL

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

860474931 | 2095B BL 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 2095B Category 6A U/UTP Cable, plenum, blue jacket, 4 pair count, variable length, reel